

JS-S100-SSH



Tapered Pipe-to-Pipe Adapter, adapts 2-3/8 in to 4 in OD pipe to 4 in to 9 in OD pipe

Product Classification

Product Type Adapter

General Specifications

Mounting Pipe-to-pipe

Taper Taper Tapered

Dimensions

Height 50.8 mm | 2 in

Width 304.8 mm | 12 in

Length 406.4 mm | 16 in

Mounting Diameter 2, maximum 228.6 mm | 9 in

Mounting Diameter 2, minimum 101.6 mm | 4 in

Mounting Diameter, maximum 101.6 mm | 4 in

Mounting Diameter, minimum 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 18.1 kg | 39.904 lb

Regulatory Compliance/Certifications

JS-S100-SSH

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system