

L1SGRIP



Support Hoisting Grip for 1/4 in coaxial cable

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Installation Tool	Required, not included
Support Clamp	Included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	101.6 mm 4 in
Leader Length, minimum	152.4 mm 6 in
Nominal Size	1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel Tin-coated bronze
----------------------	-------------------------------------

Mechanical Specifications

Pull Load Capacity	158.757 kg 350 lb
---------------------------	---------------------

Packaging and Weights

Height, packed	25.4 mm 1 in
-----------------------	----------------

L1SGRIP

Width, packed	177.8 mm 7 in
Length, packed	127 mm 5 in
Packaging quantity	1
Weight, gross	0.3 kg 0.661 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

