

MS-100



Pipe-to-Pipe Adapter, adapts 1-1/2 in to 3-1/2 in OD pipe to 4 in to 9 in OD pipe

Product Classification

Product Type Adapter

General Specifications

Mounting Pipe-to-pipe

Tower Taper Non-tapered

Dimensions

Height 50.8 mm | 2 in

Width 304.8 mm | 12 in

Length 406.4 mm | 16 in

Mounting Diameter 2, maximum 228.6 mm | 9 in

Mounting Diameter 2, minimum 101.6 mm | 4 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 11.3 kg | 24.912 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

MS-100

