

760251043 | EPX-1U-PNL-ENC-FX



EPX 1U fixed panel, accepts (3) LGX/PNL style splice cassettes, modules or panels, providing up to 36 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel Fiber patch/splice panel
Product Series	EPX

General Specifications

Application	Accepts three LGX/1000 footprint panels/cassettes Accepts three PNL-type adapter panels or ReadyPATCH® modules
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	3
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed
Total Fibers, quantity	72
Total Ports, quantity	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	412.75 mm 16.25 in

Environmental Specifications

Safety Standard	CSA 22.2 UL 1863
------------------------	--------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Weight, net

3.039 kg | 6.7 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

