

# CB-12-27LH

---



Heat-stabilized weather resistant acetal cable banding, 1/2 in x 27 in length with attached locking head, package contains 25 pieces

## Product Classification

<b>Product Type</b>	Banding
<b>Product Brand</b>	PIM-Guard®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

<b>Adapter Type</b>	Adapter
<b>Color</b>	Black
<b>Mounting</b>	Round member

## Dimensions

<b>Width</b>	12.7 mm   0.5 in
<b>Length</b>	0.686 m   2.25 ft
<b>Material Thickness</b>	1.524 mm   0.06 in

## Material Specifications

<b>Material Type</b>	Heat-stabilized weather resistant acetal
----------------------	--

## Mechanical Specifications

<b>Tensile Force</b>	1,112.055 N   250 lbf
----------------------	-----------------------

## Environmental Specifications

<b>Installation temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

<b>Packaging quantity</b>	25
---------------------------	----