

SSH-1416



SnapTak PIM-guard Adjustable Hanger, Version 1.1. Fits 14.1 mm to 16.0 mm Cables – PIM Free Polymer Construction. No Grommets Required.

Product Classification

Product Type	Hanger kit
Product Brand	SnapTak PIM-guard
Ordering Note	CommScope® standard product in Asia Pacific CommScope® standard product in Mexico, Central America, and South America CommScope® standard product in the United States and Canada

General Specifications

Accessories	Hangers
Cables per Hanger	1
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Height	32.258 mm 1.27 in
Maximum Stack Height	3
Maximum Stack Height, Coaxial	3
Width	31.496 mm 1.24 in
Length	31.496 mm 1.24 in
Compatible Diameter, maximum	16.002 mm 0.63 in
Compatible Diameter, minimum	14.097 mm 0.555 in

Electrical Specifications

Return Loss Effect	0.1 dB
DTF Effect	0.1 dB

SSH-1416

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 3.1 cm | 1.22 in

Width, packed 20.3 cm | 7.992 in

Length, packed 25.4 cm | 10 in

Packaging quantity 10

Weight, gross 0.54 kg | 1.19 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power