

SSHAK-3812



SnapStak® Hanger Kit for 3/8 in RET cable

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	40.9 mm 1.61 in
Width	22.9 mm 0.902 in
Length	66 mm 2.598 in
Compatible Cable Diameter Range	7–9 mm
Compatible Diameter, maximum	9 mm 0.354 in
Compatible Diameter, minimum	7.1 mm 0.28 in
Nominal Size	3/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	EPDM rubber Stainless steel
----------------------	-------------------------------

SSHAK-3812

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 32.5 cm | 12.795 in

Width, packed 13.5 cm | 5.315 in

Length, packed 15.5 cm | 6.102 in

Packaging quantity 10

Weight, gross 1.4 kg | 3.086 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power