

# ST-BSP40

---



## Ballast Pole, 40 ft

- Bolt-together ballast tray foundation
- No digging required
- Removable step pegs
- Collar mounting

## Product Classification

**Product Type** Monopole

## General Specifications

**Application** Multi-point telecommunications | Point-to-point communications

**Equipment Load Rating** 18 in microwave reflector | Omni antenna | Telecommunications unit

**Foundation** Non-penetrating above ground design with aggregate fill

**Monopole Capability Type** Medium duty

**Monopole Design** Round conical

**Optional Accessories** Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts

## Dimensions

**Height** 12.192 m | 40 ft

**Mounting Diameter, maximum** 304.8 mm | 12 in

**Mounting Diameter, minimum** 160.02 mm | 6.3 in

**Base Area** 8 ft x 8 ft

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Ballast tray | Ground tab | Hand holes | Lightning rod | Monopole | Safety climb systems | Safety-climb | Step pegs

**Packaging quantity** 1

# ST-BSP40

---

**Weight, net**

405.1 kg | 893.092 lb

