



Fiber Optic Pigtail, 12 fibers, Singlemode, LSH/APC to Stub, 0.9 mm diameter, multicolor, 2 m

Product Classification

| | |
|------------------------------|----------------------------|
| Regional Availability | EMEA |
| Product Type | Fiber pigtail, multi-fiber |
| Product Series | OCP |

General Specifications

| | |
|-------------------------------|---------|
| Connector A, quantity | 12 |
| Color, boot A | Green |
| Color, connector A | Green |
| Interface, Connector A | LSH/APC |
| Total Fibers, quantity | 12 |

Dimensions

| | |
|-----------------------------|-------------------|
| Cord Length | 2 m 6.562 ft |
| Diameter Over Jacket | 0.9 mm 0.035 in |

Ordering Tree

760246010 | OCP-EC-02MASEN-XX-(12COL)



| Connector/adaptor type | | |
|------------------------|------------------|------------|
| Standard C grade | Superior B grade | Type |
| S1 | SF | SC/UPC |
| S2 | SG | SC/APC 8° |
| S3 | SH | SC/APC 9° |
| L1 | LF | LC/UPC |
| L2 | LG | LC/APC |
| - | EC | LSH/APC 8° |

| Cable type | | | Fiber type |
|------------|--------|-------------------|------------|
| ASEN | 900 μm | Semi-tight jacket | A1 |
| HSEN | 900 μm | Semi-tight jacket | A2 |

| Cable length | |
|--------------|----------|
| 02 | 2 meters |

- Standard Configuration by default 900μm buffer
 buffer color : yellow
 250 μm color : natural or milky white

Optical Specifications

| | |
|---|----------------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A1, TeraSPEED® |
| Insertion Loss, maximum, connector A | 0.25 dB |
| Return Loss, minimum, connector A | 60 dB |

Environmental Specifications

| | |
|----------------------------|-------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant |

