

# CF141-XXXM-M56

---

CF141 Jumper with interface types NEX10 Male and NEX10 Male, 0.56 m



## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Series</b>	CF141-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	CF141-50
<b>Interface, Connector A</b>	NEX10 Male
<b>Interface, Connector B</b>	NEX10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	0.56 m   1.837 ft
<b>Nominal Size</b>	0.141 in

## Electrical Specifications

<b>3rd Order IMD</b>	-117 dBm
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
100–3000 MHz	1.135	24

## Jumper Assembly Sample Label

# C141-XMxm-M56

---

Batch    Manufacturing Date (two digit year and week)

Manufacturing Plant    Product Revision

**ANDREW**  
an Amphenol company

0123456789    US22    1240    /A

**F4-DMDM-2M-D**    Part Number

2 M (6.562 FT)  
SUREFLEX ASSEMBLY  
U.S. PATENT 5802710

Product of UNITED STATES    12US220001242    Serial Number