

CF141-XXXM-M92

CF141 Jumper with interface types NEX10 Male and NEX10 Male, 0.92 m



Product Classification

Product Type	Braided cable assembly
Product Series	CF141-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CF141-50
Interface, Connector A	NEX10 Male
Interface, Connector B	NEX10 Male
Specification Sheet Revision Level	A

Dimensions

Length	0.92 m 3.018 ft
Nominal Size	0.141 in

Electrical Specifications

3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
100–3000 MHz	1.135	24

Jumper Assembly Sample Label

C141-XMXM-M92



Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

