# FGSB-MSHS-E



## FiberGuide® Vertical Straight Section with Slots, 4x2in, Black

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeSlotted verticalProduct BrandFiberGuide®

Product Series FGS

# General Specifications

Product Feature Slotted

Color Black

Orientation Vertical

Section Type Straight Section

#### **Dimensions**

 Height
 50.8 mm | 2 in

 Width
 101.6 mm | 4 in

 Length
 1829 mm | 72.008 in

**System Dimensions** 102 mm x 51 mm (4 in x 2 in)

# Ordering Tree



# FGSB-MSHS-E



#### **Section Color**

9	empty	yellow
	В	black

#### **Section Length**

11	empty	6 ft
	10	10 ft
	12	12 ft

#### **Section Size**

10	А	4 x 4 in
	В	4 x 6 in
	С	2 x 2 in
	D	4 x 4 in, slotted duct, 2 in slot spacing
	F	4 x 12 in
	F-CF	4 x 12 in, with center divider
	G	2 x 6 in
	н	4 x 24 in
	К	2 x 4 in, slotted duct, 2 in slot spacing
	STOR-B	4 x 6 in, with slack storage spools
	STOR-G	2 x 6 in, with slack storage spools
	STOR-F	4 x 12 in, with slack storage spools

# Material Specifications

Material Type Engineering Thermoplastic

# **Environmental Specifications**

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

# Packaging and Weights

Packaging quantity 1

**Weight, net** 1.005 kg | 2.216 lb

# Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

COMMSC PE®

# FGSB-MSHS-E



