
ZB-H4



Horizontal Z-bracket, 11 in, for seven coaxial cable runs

Product Classification

Portfolio CommScope®
Product Type Bracket kit

Ordering Note CommScope® standard product (Global)

General Specifications

Cable Runs, quantity 7
Hole, quantity 7

Mounting Walls

Dimensions

 Height
 50.8 mm | 2 in


 Width
 152.4 mm | 6 in

 Length
 279.4 mm | 11 in

 Hole Size
 3/4 in | 7/16 in

ZB-H4

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Z-bracket

Packaging quantity 1

Weight, net 1.2 kg | 2.646 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

Page 2 of 3

ZB-H4





* Footnotes

Wind Rating

BWS-Base Wind Speed; FBC-Florida Building Code