

FST-F3DF-MT-D

Fiber Optic Splice Tray, 24 splice capacity

Product Classification

Regional Availability Latin America | North America

Product Type Fiber splice tray

General Specifications

Application For use with FDF splice panels

Color Black

Splicing Capacity, maximum 24

Splicing Type Mass fusion

Environmental Specifications

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

