# UKXMXUCAM

#### **Base Product**



Ultra Low Loss (ULL) Multimode OM4 MPO12 (Pinned) to Unconnectorized, Armored Pre-terminated Trunk Cable, 144-Fiber, Low Smoke Zero Halogen (LSZH)

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration | Not available in the United States or Canada

General Specifications

Connector A, quantity 12

Color, boot A Black

Color, connector A Aqua

Connector B, quantity 0

Color, boot B Black

Color, connector B Aqua

Construction Type Armored | Stranded

Furcation Color Aqua

Interface, Connector A MPO-12/UPC Male

Interface Feature, connector A Pinned

Interface, Connector B Unterminated

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 144

**Dimensions** 

**COMMSCOPE®** 


# UKXMXUCAM

Breakout Length 33 in

Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

#### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

**Fiber Type** OM4, LazrSPEED®

## **Environmental Specifications**

Operating Temperature $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )Environmental SpaceDual Rated LSZH/Riser | Indoor

#### Included Products

760120105 – Fiber indoor cable, LazrSPEED® Riser/LSZH rated, MPO Trunk, interlocking aluminum armored, N-144-MZ-5K-F12AQ Multimode OM4, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Feet jacket marking, Aqua

Multimode OM4, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Feet jacket marking, Aquijacket color

Jacket Cold

860366228 – MP012, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm

**COMMSCOPE®**