## 760249179 | 26" Pole Cab with 12" Integrated Pole Shaft



Decorative Pole Cab with an Integrated Pole supporting 4G/5G/mmWave technologies as well as smart devices

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center /OVP and Disconnect and integrated AC/DC rectifier options

Also available with a 30"x30" base for additional capacity -Multi Carrier capable

## **OBSOLETE**

## Product Classification

Portfolio CommScope®

Product Type Pole cab
Product Brand Metro Cell

Ordering Note CommScope® standard product with terms

**Warranty** One year

General Specifications

**Color** Light Gray (RAL 7035)

Color Options Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green (RAL 6012) | Brown (RAL

8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Umbra Grey (RAL 7022)

Compatible Foundation Type Poured Concrete | Pre-Cast Concrete

Compatible Smart Devices Cameras | Digital Signage | Emergency Call Station | Environmental

Monitoring | Security Lighting | WIFI

**Cooling** Fan Cooling

Power Supply Compatibility DELTA 2.0 | PSU-AC-08

Radio Compatibility, Ericsson (1) 8843/4449 dual-band high power radio and (2) PSU-

AC08 | 1281 | 220x | 440x | 4426 | 4478 | 6701

Radio Compatibility, Nokia AEUB | AEWB | AEWD

/AEWE | AHFB | AHFIA | AHFIB | AHIA | AHIB | AHLBA | AHLBBA | AZRB

Radio Compatibility Samsung AT1K01 | AT1K02 | AT1K0X | DELTA 2.0 | Diplexer | HT1K01 | Power

Distribution | RF4402D-D1A | RFV01U-D1A | RFV01U-D2A | RT2201-46A | RT4401-

48A

Page 1 of 2



## 760249179 | 26" Pole Cab with 12" Integrated Pole Shaft

Radios Included None

**Dimensions** 

**Height Note** 4 ft tall Equipment Cabinet Base

 Pole Height Options
 7.925 m | 26 ft

 Width
 660.4 mm | 26 in

 Depth
 660.4 mm | 26 in

**Depth Note** Square

**Pole Diameter** 323.85 mm | 12.75 in

**Electrical Specifications** 

**Power/Fiber Input**AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate
Finish Concealment Covers Powder coated

Material Type Galvanized steel

**Environmental Specifications** 

Thermal Compliance GR-487

\* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

**Pole Height Options** Overall AGL Standard Height