

FPX-1FRHOZ240



FPX Fiber Optic Termination Panel with HMFOC tether, 1RU, 19in, Singlemode, 24 fiber, LC/APC Connector to 2x12 fiber HMFOC, putty white

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Series | FPX |

General Specifications

| | |
|---|-----------------------|
| Functionality | Patching |
| Adapter Packs Included, quantity | 2 |
| Body Style | Symmetrical |
| Color | Putty white |
| Color, front | Putty white |
| Growth Configuration | Partially loaded |
| Interface, front | LC |
| Interface Feature, front | APC |
| Patching Capacity, maximum | 24 |
| Rack Type | EIA 19 in EIA 23 in |
| Rack Units | 1 |
| Shelf Movement | Sliding |
| Total Fibers, quantity | 24 |
| Total Ports, quantity | 24 |

Dimensions

| | |
|--------------------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |
| Depth | 304.8 mm 12 in |
| Cable Stub Length | 0 m 0 ft |

Material Specifications

FPX-1FRHOZ240

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1