

# EG4847-000 | FIST-FSASA2-164-1P-X



FIST® Fiber Splice Tray with Field Installable Splitter, symmetrical ratio, 1x64, Planar component, grade P

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China   EMEA   India   Latin America   North America
<b>Product Type</b>	Splitter splice tray
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-FSASA2

## General Specifications

<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Application</b>	For use with FIST fiber splice closures
<b>Distribution Type</b>	1 x 64 splitter
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail
<b>Split Ratio</b>	50/50
<b>Splitter, quantity</b>	1

## Optical Specifications

<b>Performance Grade</b>	Grade P (PLC, standard)
--------------------------	-------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

