

2-1499418-1 | 1061F Cat5e U/UTP WHT 25/24 R4000



1061F Cat5e U/UTP Cable, Riser, White Jacket, 25 pair count, 4000 ft (1220 M) length reel

Product Classification

Regional Availability	Asia Latin America North America
Portfolio	CommScope®
Product Type	Twisted pair cable

General Specifications

Product Number	1061F
ANSI/TIA Category	5e
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	50
Jacket Color	White
Pairs, quantity	25
Transmission Standards	ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class D

Dimensions

Cable Length	304.8 m 1000 ft
Diameter Over Jacket, nominal	12.7 mm 0.5 in
Conductor Gauge, singles	24 AWG

Electrical Specifications

Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

2-1499418-1 | 1061F Cat5e U/UTP WHT 25/24 R4000

Safety Voltage Rating 300 V

Material Specifications

Conductor Material Bare copper

Insulation Material High density polyethylene (HDPE)

Jacket Material PVC

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Environmental Space Non-plenum

Packaging and Weights

Cable weight 229.177 kg/km | 154 lb/kft

Packaging Type Reel