

RT-DF12-3-126



High Capacity DUAL Non-Penetrating Roof Frame, 12 ft face, three 2-7/8 in OD x 126 in pipes

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating

Pipe, quantity 3

Dimensions

Height 3,200.4 mm | 126 in

Face Width 3.81 m | 12.5 ft

Width 3,810 mm | 150 in

Length 2,377 m | 7.8 ft

Pipe Length 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Pipe Outer Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Ballast tray | Frame | Plain end pipes (3)