

RT-DF12-4-126



High Capacity DUAL Non-Penetrating Roof Frame, 12 ft face, four 2-7/8 in OD x 126 in pipes

Product Classification

Product Type	Non-penetrating roof frame
Ordering Note	NSTD445 Compliant

General Specifications

Mounting	Non-penetrating
Pipe, quantity	4

Dimensions

Height	3,200.4 mm 126 in
Face Width	3.81 m 12.5 ft
Width	3,810 mm 150 in
Length	2,377 m 7.8 ft
Pipe Length	3,200.4 mm 126 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating Test Method	TIA/EIA-222
--------------------------------	-------------

Packaging and Weights

Included	Ballast tray Frame Plain end pipes (4)
-----------------	--

RT-DF12-4-126

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

