

LS2-HMHM-5M-D

D-CLASS LSF2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 5 m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX® SureFlex®
Product Series	LSF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	5 m 16.404 ft
Nominal Size	3/8 in

Electrical Specifications

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

Logo Image

LS2-HMHM-5M-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-970 MHz	1.065	30
1700-2200 MHz	1.065	30
2200-2700 MHz	1.083	28
3400-3800 MHz	1.222	20
4000-6000 MHz	1.222	20

Jumper Assembly Sample Label

LS2-HMHM-5M-D



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition