



Carrier Access Point with MIMO 2x2 Radio Module for Low Power USA 700, USA 750, LMR 750, AWS 1700, PCS 1900, and C-Band Applications, Copper fed, PoE++

## Product Classification

<b>Product Type</b>	Access point
<b>Product Brand</b>	ERA®
<b>Product Series</b>	UAP2

## General Specifications

<b>Antenna Type</b>	MIMO Antenna
<b>Fan Kit</b>	Included
<b>Fed Type</b>	Copper fed
<b>Note</b>	Detailed Product Specifications are available. Please contact your local ANDREW representative.
<b>Power Class</b>	Low
<b>Powering Type</b>	PoE powered

## Electrical Specifications

<b>License Band</b>	AWS 1700   C-Band   LMR 750   PCS 1900   USA 700   USA 750
---------------------	--

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

