760254728 | C-006-CN-8W-M06BK/28G/AY/E



Indoor/Outdoor Low Smoke Zero Halogen, TeraSPEED® Central Loose Tube Fiber Optic Cable, 6-fiber, Singlemode OS2, Gel-filled, black

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-CN

General Specifications

Cable TypeLoose tubeSubunit TypeGel-filledJacket ColorBlackJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760254728 INT/EXT GEL LOOSE TUBE

6X9/125 OS2 EN50575 CLASS D [Serial NUMBER] [METRE MARK]

Fibers per Subunit, quantity 6

Total Fiber Count 6

Dimensions

 Cable Length
 2000 m | 6,561.68 ft

 Diameter Over Jacket
 6.4 mm | 0.252 in

Mechanical Specifications

Minimum Bend Radius, loaded140 mm5.512 inMinimum Bend Radius, unloaded130 mm5.118 inTensile Load, long term, maximum400 N89.924 lbfTensile Load, short term, maximum500 N112.404 lbf

Optical Specifications

Fiber Type OS2

Page 1 of 2

760254728 | C-006-CN-8W-M06BK/28G/AY/E

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.35 dB/km @ 1,300 nm

Standards Compliance IEC 60794-1 | TIA-492CAAB (OS2)

Environmental Specifications

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

EN50575 CPR Cable EuroClass Fire Performance Eca

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Cable weight 33 kg/km | 22.175 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

