


FGSB-MSHS-F10



FiberGuide® Horizontal Straight Section, 4x12in, 10ft Length, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Straight section
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Straight section

Dimensions

Length	3048 mm 120 in
System Dimensions	102 mm x 305 mm (4 in x 12 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net	5.04 kg 11.111 lb
--------------------	---------------------

Regulatory Compliance/Certifications

FGSB-MSHS-F10

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

