


2-599692-2 | O-008-CA-5K-M08BK/28G/HD



Outside Plant Fiber Optic Cable, HDPE, 8-fiber, Multimode, OM4, loose tube, gel-filled, 2000 m

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-CA

General Specifications

Armor Type	Corrugated steel
Cable Type	Loose tube
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB SYSTEM F.O. CABLE X-599692-2 CSA GEL LOOSE TUBE 8X50/125 OM4 HDPE (Serial NUMBER) (METRE MARK)
Fibers per Subunit, quantity	8
Total Fiber Count	8

Dimensions

Cable Length	2000 m 6,561.68 ft
Diameter Over Jacket	10 mm 0.394 in

Material Specifications

Jacket Material	High density polyethylene (HDPE)
------------------------	----------------------------------

Mechanical Specifications

2-599692-2 | O-008-CA-5K-M08BK/28G/HD

Minimum Bend Radius, loaded	200.7 mm 7.902 in
Minimum Bend Radius, unloaded	160 mm 6.299 in
Tensile Load, long term, maximum	625 N 140.506 lbf
Tensile Load, short term, maximum	1200 N 269.771 lbf
Flex	25 cycles

Optical Specifications

Fiber Type	OM4, LazrSPEED®
-------------------	-----------------

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.70 dB/km @ 1,300 nm 3.50 dB/km @ 850 nm
Standards Compliance	TIA-492AAAD (OM4)

Environmental Specifications

Installation temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

Packaging and Weights

Cable weight	104 kg/km 69.885 lb/kft
---------------------	---------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-5K-LT	- LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber
----------	---

* Footnotes

2-599692-2 | 0-008-CA-5K-M08BK/28G/HD

Operating Temperature Specification applicable to non-terminated bulk fiber cable