

SRC9-UAA1010A000



NOVUX™ Specialty Range Closure 10 replacement closure housing including 2 tie-wraps

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

Product Classification

Regional Availability	Asia EMEA Latin America North America
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	SRC10

General Specifications

Cable Capacity, Drop	2 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 2 Round 2–6.2 mm (0.08–0.24 in)
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Compressed gel
Cable Termination Attachments, quantity	2
Closure Sealing Type	Hinged with latch
Closure Style	In-line
Color	Black
Mounting	Handhole Partially buried Pedestal Wall/Pole Mount, mounting kit included
Network Area Type	Drop
Port, quantity	2
Splice Tray Included, quantity	1
Splicing Capacity, Mass Fusion, maximum	12
Splicing Capacity, maximum	4
Splicing Capacity, Single Fusion, maximum	4

SRC9-UAA1010A000

Splicing Type, Supported Single fusion

Splitter Type No splitter

Dimensions

Width 76 mm | 2.992 in

Depth 26 mm | 1.024 in

Length 210 mm | 8.268 in

Cable Entry Drop Port Diameter 6 mm (0.24 in) mm

Material Specifications

Material Type Impact-resistant polymer

Optical Specifications

Fiber Type G.657.A1 | G.657.A2 | G.657.B3

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Above ground | Below ground | Direct burial

Qualification Standards IEC 60529, IP68 + 1 m waterhead | IEC 61753-1, category G

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Weight, net 0.157 kg | 0.346 lb