VZWSMART-MSK12 | UNIVERSAL CROSSOVER PLATE



UNIVERSAL CROSSOVER PLATE

Universal Crossover Plate, connects up to 4-1/2" OD x 4-1/2" OD Pipe (Pipe not included)

Product Classification

Product Type Clamp plate

Ordering Note ANDREW® non-standard product

General Specifications

Mounting Crossover plate

Dimensions

Mounting Diameter 2, maximum114.3 mm | 4.5 inMounting Diameter 2, minimum42.164 mm | 1.66 inMounting Diameter, maximum114.3 mm | 4.5 inMounting Diameter, minimum42.164 mm | 1.66 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Hardware | Plates

Packaging quantity

Weight, net 10 kg | 22.046 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted





VZWSMART-MSK12 | UNIVERSAL CROSSOVER PLATE