COMMSCOPE®

CMC74-36E, CMC74-36C, CMC74-36B, CMC85-36 Macro Cabinet Ordering Guide 2022



Contents

CMC74-36E Cabinet Solutions	4
Model 760250058	5
Model 760250059	6
CMC74-36C Cabinet Solutions	7
Model 760251249	8
Model 760251637	9
Model 760251256	10
Model 760251638	11
CMC85-36C Cabinet Solutions	12
Model 760250650	13
Model 760250651	14
Model 760250955	15
Model 760250956	16
CMC74-36B Cabinet Solutions	17
Model 760250540	18
Model 760250963	19
CommScope CMC Cabinet Aftermarket Kit (AMK) Options	20
CMC Cabinets Aftermarket (AMK) Options	21
CMC Cabinets Aftermarket (AMK) Options - Continued	22




CMC74-36E Equipment and Power Cabinet with 4 kW Air Conditioner


CMC74-36E Cabinet Solutions



CMC74-36E Equipment and Power Cabinet with 4 kW Air Conditioner

Model 760250058





CMC Cabinet Ordering Number

Orderable Number	Description
	CMC74-36E, Equipment Cabinet, 4 kW Air Conditioner, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description
Field Replacement Units (FRUs)	
760250972	Front Door Assembly, 4kW Air Conditioner, CMC74-36E
760250922	Handle, Front Door
760250960	Rear Door Assembly
760250935	4 kW Air Conditioner, DC
760250926	Interchangeable Conduit Panel, Rear
760250927	Solar Shield, Top
Aftermarket Kits (AMKs) **	
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B
760250933	6" High Plinth, Cabinet Mounting
** Additional AMKs can be found on pages 21-22.	

Cabinet Features

Dimensions:

- Overall 74" H X 43.7" D X 36" W (standard height, depth with air conditioner)
 - With Optional 6" Plinth 80" H X 43.7" D X 36" W (depth with air conditioner)
 - Footprint 37" D X 36" W
 (depth without air conditioner)

Weight: 525 lbs. (238 kg)

Weight as Shipped: 701 lbs. (318 kg)

— Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg])

Equipment Compartment

- 4 kW Air Conditioner, DC*
- Adjustable Equipment Rack System, Up to 49 RU
- Up to 40 RU of 23" EIA Horizontal Rack Space
- Up to 9 RU of 19" EIA Vertical Rack Space
- OVP Vertical Side Mounting Options
- Allows more Horizontal Rack Space for Equipment
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door
- Two interchangeable Rear Port Panels
 - Cabinet Ships with One Conduit Knockout Panel and One Blank Panel
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks


Telcordia GR-487 Compliant Safety Agency Listed


* Hardened equipment to -40° C to +65° C



CMC74-36E Equipment and Power Cabinet with 4 kW Thermosiphon

Model 760250059





CMC Cabinet Ordering Number

Orderable Number	Description
	CMC74-36E, Equipment Cabinet with 4kW Thermosiphon, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250973	Front Door Assembly, with 4kW Thermosiphon, CMC74-36E	
760250922	Handle, Front Door	
760250960	Rear Door Assembly	
760250923	Thermosiphon, 4 kW, DC	
760250926	Interchangeable Conduit Panel, Rear	
760250927	Solar Shield, Top	
Aftermarket Kits (AMKs)		
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250931	Air Conditioner, DC; 4 kW, Upgrade	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can be found on pages 21-22.		

Cabinet Features

Dimensions:

- Overall 74" H X 43.7" D X 36" W (standard height, depth with thermosiphon)
- With Optional 6" Plinth 80" H X 43.7" D X 36" W (depth with thermosiphon)
- Footprint 37" D X 36" W (depth without thermosiphon)

Weight: 512 lbs. (232 kg)

Weight as Shipped: 688 lbs. (312 kg)

- Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg])

Equipment Compartment

- 4 kW Thermosiphon, DC, Cooling*
- Adjustable Equipment Rack System, Up to 49 RU
 - Up to 40 RU of 23" EIA Horizontal Rack Space
 - Up to 9 RU of 19" EIA Vertical Rack Space
- OVP Vertical Side Mounting Options
- Allows more Horizontal Rack Space for Equipment
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door
- Two Interchangeable Rear Port Panels
- Cabinet Ships with One Conduit Knockout Panel and One Blank Panel
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Telcordia GR-487 Compliant Safety Agency Listed

* Hardened equipment to -40° C to +65° C




CMC74-36C Equipment, Power, and Battery Cabinet, Cabinet Solutions


CMC74-36C Cabinet Solutions



CMC74-36C Equipment, Power, and Battery Cabinet, VRLA, 3-String, 3 kW Thermosiphon, with 1 kW Battery Air Conditioner with 500 W Heater

Model 760251249





CMC Cabinet Ordering Number

Orderable Number	Description
	CMC74-36C, Equipment and Battery Cabinet, VRLA, 3-String, 3 kW Air Conditioner, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250922	Handle, Front Door	
760250960	Rear Door Assembly, CMC74-36C	
760250925	1 kW Battery HVAC with 1 kW Heater	
760250926	Interchangeable Conduit Panel, Rear	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
760253581	Front Door Assembly with 3 kW Air Conditioner, DC	
760253582	3 kW Air Conditioner, DC	
Aftermarket Kits (AMKs) **		
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can be found on pages 21-22.		

Cabinet Features

Dimensions:

- Overall 74" High X 43.7" Deep X 36" Wide (standard height, depth with air conditioner)
 - With Optional 6" Plinth 80" H X 43.7" D X 36" W (depth with air conditioner)
 - Footprint 37" D X 36" W (depth without air conditioner)

Weight: 909 lbs. (412 kg)

Weight as Shipped: 1019 bs. (462 kg)

- Note: Cabinet Weights are without Plinth (178 lbs. [81 kg])

Equipment Compartment

- 3 kW Air Conditioner, DC*
- Up to 24 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 20 RU of 23" EIA Horizontal Rack Space
 - 4 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
- Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment


- 2 Battery Shelves, 3-String Capacity of VRLA, 48 V
 - Battery Temperature Probes Included, 2 each only regardless of number of strings.
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switch
 - Battery Cabling and the 250A Circuit Breakers Included
- 1kW Battery Air Conditioner with 500 W Heater, DC*

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22



CMC74-36C, Equipment, Power, and Battery Cabinet, VRLA, 3-String, 3 kW Air Conditioner, with 1 kW Battery Air Conditioner with 500 W Heater

Model 760251637



CMC Cabinet Ordering Number

Orderable Number	Description
	CMC74-36C, Equipment and Battery Cabinet, VRLA, 3-String, 3 kW Thermosiphon, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Units (FRUs)		
760XXXYYY	Front Door Assembly, with 3 kW Thermosiphon, CMC74-36C	
760250922	Handle, Front Door	
760250960	Rear Door Assembly	
760XXXYYY	Thermosiphon, 3 kW, DC	
760250926	Interchangeable Conduit Panel, Rear	
760250927	Solar Shield, Top	
Aftermarket Kits (AMK	Aftermarket Kits (AMKs)	
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250931	Air Conditioner, DC, 3 kW, Upgrade	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can be found on pages 21-22.		

Cabinet Features

Dimensions:

- Overall 74" H X 43.7" D X 36" W (standard height, depth with thermosiphon)
- With Optional 6" Plinth 80" H X 43.7" D X 36" W (depth with thermosiphon)
- Footprint 37" D X 36" W (depth without thermosiphon)

Weight: 896 lbs. (406 kg)

Weight as Shipped: 1006 lbs. (456 kg)

- Note: Cabinet Weights are without Plinth (178.4 lbs. [81 kg])

Equipment Compartment

- 3 kW Thermosiphon, DC, Cooling*
- \bullet Up to 24 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 20 RU of 23" EIA Horizontal Rack Space
 - 4 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
- Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment


- 2 Battery Shelves, 3-String Capacity of VRLA, 48 V
- Battery Temperature Probes Included, 2 each only regardless of number of strings.
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switch
 - Battery Cabling and the 250A Circuit Breakers Included
- 1kW Battery Air Conditioner with 500 W Heater, DC*

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22



CMC74-36C Equipment, Power, and Battery Cabinet, NiCd, 3-String, 3 kW Thermosiphon, DC

Model 760251256



CMC Cabinet Ordering Number

Orderable Number	Description
760251256	CMC74-36C, Equipment and Battery Cabinet,
	NiCd, 3-String, 3 kW Air Conditioner, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250922	Handle, Front Door	
760250960	Rear Door Assembly, CMC74-36C	
760250926	Interchangeable Conduit Panel, Rear	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
760253581	Front Door Assembly with 3 kW Air Conditioner, DC	
760253582	3 kW Air Conditioner, DC	
Aftermarket Kits (AMKs)		
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can be found on pages 21-22.		

Cabinet Features

Dimensions:

- Overall 74" High X 43.7" Deep X 36" Wide (standard height, depth with air conditioner)
- With Optional 6" Plinth 80" H X 43.7" D X 36" W (depth with air conditioner)
- Footprint 37" D X 36" W (depth without air conditioner)

Weight: 848 lbs. (384 kg)

Weight as Shipped: 958 bs. (434 kg)

- Note: Cabinet Weights are without Plinth (178 lbs. [81 kg])

Equipment Compartment

- 3 kW Air Conditioner, DC*
- Up to 24 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 20 RU of 23" EIA Horizontal Rack Space
 - 4 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
 - Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment


- 2 Battery Shelves, 3-String Capacity of NiCd, 48 V
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switch
 - Battery Cabling and the 250A Circuit Breakers Included
- Optional 1 kW Heater**

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22



CMC74-36C Equipment, Power, and Battery Cabinet, NiCd, 3-String, 3 kW Air Conditioner, DC

Model 760251638



CMC Cabinet Ordering Number

Orderable Number	Description
760251638	CMC74-36, Equipment and Battery Cabinet, NiCd, 3-String, with 3 kW Thermosiphon, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760XXXYYY	Front Door Assembly, with 3 kW Thermosiphon, CMC74-36C	
760250922	Handle, Front Door	
760XXXYYY	Thermosiphon, DC, 3 kW	
760250960	Rear Door Assembly, CMC74-36	
760250926	Interchangeable Knockout Panel, Rear	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
Aftermarket Kits (AMK	Aftermarket Kits (AMKs)	
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250931	Air Conditioner, DC, 3 kW, Upgrade	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can b	pe found on pages 21-22.	

Cabinet Features

Dimensions:

- Overall 74" H X 43.7" D X 36" W (standard height, depth with thermosiphon)
- With Optional 6" Plinth 80" H X 43.7" D X 36" W (depth with thermosiphon)
- Footprint 37" D X 36" W (depth without thermosiphon)

Weight: 835 lbs. (379 kg)

Weight as Shipped: 946 lbs. (429 kg)

— Note: Cabinet Weights are without Plinth (178.4 lbs. [81 kg])

Equipment Compartment

- 3 kW Thermosiphon, DC, Cooling*
- Up to 24 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 20 RU of 23" EIA Horizontal Rack Space
 - 4 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
 - Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment

- 2 Battery Shelves, 3-String Capacity of NiCd, 48 V
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switch
 - Battery Cabling and the 250A Circuit Breakers Included
- Optional 1 kW Heater**

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22




CMC85-36C Equipment, Power, and Battery Cabinet Solutions

CMC85-36C Cabinet Solutions



CMC85-36C Equipment, Power, and Battery Cabinet, VRLA, 3-String, 4 kW Thermosiphon, with 1 kW Battery Air Conditioner with 500 W Heater

Model 760250650



CMC Cabinet Ordering Number

Orderable Number	Description
	CMC85-36C, Equipment and Battery Cabinet, VRLA, 3-String, with 4 kW Thermosiphon, 1kW Air Conditioner with 500 kW Heater

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250921	Front Door Assembly, with 4 kW Thermosiphon and 1 kW Battery HVAC with 1 kW Battery Heater, CMC85-36C	
760250922	Handle, Front Door	
760250923	4 kW Thermosiphon, DC	
760250924	Rear Door Assembly, CMC85-36C	
760250925	1 kW Battery HVAC with 500 W Heater, DC	
760250926	Interchangeable Conduit Panel, Rear	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
Aftermarket Kits (AMK	Aftermarket Kits (AMKs)	
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760XXXYYY	HVAC, 4 kW, DC, Upgrade	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can be found on pages 21-22.		

Cabinet Features

Dimensions:

- Overall 85" H X 43.7" D X 36" W (standard height, depth with thermosiphon
 - With Optional 6" Plinth 92" H X 43.7" D X 36" W (depth with thermosiphon)
- Footprint 37" D X 36" W (depth without thermosiphon)

Weight: 727 lbs. (330 kg)

Weight as Shipped: 1118 lbs. (507 kg)

- Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg])

Equipment Compartment

- 4 kW DC Thermosiphon, Cooling*
- Up to 35 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 27 RU of 23" EIA Horizontal Rack Space
 - 8 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door with Lower Vent
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
- Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment


- 2 Battery Shelves, 3-String Capacity of VRLA Batteries, 48 V
- Battery Temperature Probes Included, 2 each only regardless of number of strings.
- Battery Cabling and the 250A Circuit Breakers Included
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switches
- 1 kW Battery Air Conditioner with 500 W Heater, DC*

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22



CMC85-36C Equipment, Power, and Battery Cabinet, VRLA, 3-String, 4 kW Air Conditioner, with 1 kW Battery Air Conditioner with 500 W Heater

Model 760250651



CMC Cabinet Ordering Number

Orderable Number	Description
	CMC85-36C, Equipment and Battery Cabinet, VRLA, 3- String, 4 kW Air Conditioner, and 1 kW Battery Air Conditioner with 500 W Heater, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250922	Handle, Front Door	
760250924	Rear Door Assembly, CMC85-36C	
760250925	1 kW Battery HVAC with 500 W Heater	
760250926	Interchangeable Conduit Panel, Rear	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
760250934	Front Door Assembly, 4 kW Air Conditioner, CMC85-36C	
760250935	4 kW Air Conditioner, DC	
Aftermarket Kits (AMKs) **		
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250933	AMK, 6" High Plinth, Cabinet Mounting	
** Additional AMKs can be found on pages 21-22.		

Cabinet Features

Dimensions:

- Overall 85" High X 43.7" Deep X 36" Wide (standard height, depth with air conditioner)
- With Optional 6" Plinth 92" H X 43.7" D X 36" W (depth with air conditioner)
- Footprint 37" D X 36" W (depth without air conditioner)

Weight: 741 lbs. (336 kg)

Weight as Shipped: 1131 bs. (513 kg)

- Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg])

Equipment Compartment

- 4 kW Air Conditioner, DC*
- Up to 35 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 27 RU of 23" EIA Horizontal Rack Space
 - 8 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
- Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment


- 2 Battery Shelves, 3-String Capacity of VRLA, 48 V
- Battery Temperature Probes Included, 2 each only regardless of number of strings.
- Battery Cabling and the 250A Circuit Breakers Included
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switch
- 1 kW Battery Air Conditioner with 500 W Heater, DC*

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22



CMC85-36C Equipment, Power, and Battery Cabinet, NiCd, 3-String, with 4 kW Thermosiphon

Model 760250955



CMC Cabinet Ordering Number

Orderable Number	Description
	CMC85-36, Equipment and Battery Cabinet, NiCd, 3-String, with 4 kW Thermosiphon

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250921	Front Door Assembly, with 4kW Thermosiphon, CMC85-36	
760250922	Handle, Front Door	
760250923	Thermosiphon, DC, 4 kW	
760250924	Rear Door Assembly, CMC85-36	
760250926	Interchangeable Knockout Panel, Rear	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
Aftermarket Kits (AMK	Aftermarket Kits (AMKs)	
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760XXXYYY	4 kW HVAC, DC, Upgrade	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can l	pe found on pages 21-22.	

Cabinet Features

Dimensions:

- Overall 85" H X 43.7" D X 36" W (standard height, depth with thermosiphon
 - With Optional 6" Plinth 92" H X 43.7" D X 36" W (depth with thermosiphon)
- Footprint 37" D X 36" W (depth without thermosiphon)

Weight: 717 lbs. (270.8 kg)

Weight as Shipped: 987 lbs. (325 kg)

- Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg])

Equipment Compartment

- 4 kW DC Thermosiphon, Cooling*
- \bullet Up to 35 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 27 RU of 23" EIA Horizontal Rack Space
 - 8 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door with Lower Vent
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
- Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment


- 2 Battery Shelves, 3-String Capacity of NiCd Batteries, 48 V
 - Battery Temperature Probes Included, 2 each only regardless of number strings
 - Battery Cabling and the 250A Circuit Breakers Included
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switches
- Optional 1 kW Heater**

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22



CMC85-36C Equipment Power, and Battery Cabinet, NiCd, 3-String, with 4 kW Air Conditioner, DC

Model 760250956



CMC Cabinet Ordering Number

Orderable Number	Description
	CMC85-36, Equipment and Battery Cabinet, NiCd, 3-String, 4 kW Air Conditioner, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250922	Handle, Front Door	
760250924	Rear Door Assembly, CMC85-36	
760250926	Interchangeable Conduit Panel, Rear	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
760250934	Front Door Assembly, 4 kW Air Conditioner, DC, CMC85-36	
760250935	4kW Air Conditioner, DC	
Aftermarket Kits (AMKs) **		
760246443	Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can be found on pages 21-22.		

Cabinet Features

Dimensions:

- Overall 85" H X 43.7" D X 36" W (standard height, depth with air conditioner
- With Optional 6" Plinth 92" H X 43.7" D X 36" W (depth with air conditioner)
- Footprint 37" D X 36" W
 (depth without air conditioner)

Weight: 730 lbs. (331 kg)

Weight as Shipped: 1120 bs. (508 kg)

Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg])

Equipment Compartment

- 4 kW Air Conditioner, DC*
- Up to 35 RU of 19"/23" Total Horizontal/Vertical EIA Rack Space
 - 27 RU of 23" EIA Horizontal Rack Space
 - 8 RU of 19" EIA Vertical Rack Space
- Cabinet Light
- 4-Position GFCI Outlet
- Hinged Rear Access Door with Lower Vent
- Cabinet Ships with One Rear Conduit Knockout Panel at the Top.
- Note: Roxtec, 4-inch, Rear Panel available as optional order**.
- Knockouts on Left and Right Sides, Rear
- Solar Shield, Top
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks

Battery Compartment

- 2 Battery Shelves, 3-String Capacity of NiCd Batteries, 48 V
 - Battery Temperature Probes Included, 2 each only regardless of number of strings.
 - Battery Cabling and the 250A Circuit Breakers Included
- Master Circuit Breaker String Panel with 3 each 250-amp String Circuit Breaker Switches
- Optional 1 kW DC Heater**

Telcordia GR-487 Compliant

Safety Agency Listed

- * Hardened equipment to -40° C to +65° C
- ** Refer to CMC Cabinet AMK Options on pages 21-22



CMC74-36B Battery Cabinet Solutions


CMC74-36B Cabinet Solutions




CMC74-36B VRLA Battery Cabinet for 6 Strings, HVAC Door with Heater

Model 760250540







CMC Cabinet Order Information

Orderable Number	Description
	CMC74-36B, VRLA Battery Cabinet, 6-String, 1 kW HVAC with 500 W Heater, DC

Field Replacement Units and Aftermarket Kits

Orderable Number	Description	
Field Replacement Un	Field Replacement Units (FRUs)	
760250922	Handle, Front Door	
760250925	1 kW HVAC with 500 W Heater, DC	
760250927	Solar Shield, Top	
760250928	Circuit Breaker, Battery String, 250 A	
760250958	Front Door Assembly, 1 kW HVAC with 500 W Heater, CMC74-36B	
760250961	Solar Shield, Side	
760253587	Rear Door Assembly, CMC74-36B	
After Market Kits (AM	After Market Kits (AMKs)	
760246443	AMK, Interconnect, 3PR, 4/0, 2", CMC74-36B	
760250933	6" High Plinth, Cabinet Mounting	
** Additional AMKs can I	pe found on pages 21-22.	

Cabinet Features

Dimensions:

- Overall 74" H X 43.7" D X 36" W (standard height, depth with air conditioner)
- With Optional 6" Plinth 80" H X 43.7" D X 36" W (depth with air conditioner)
- Footprint 37" D X 36" W
 (depth without air conditioner)

Weight: 1060 lbs. (481 kg) - for 6-String Cabinet

Weight as Shipped: 1237 lbs. (561 kg)

Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg]).

Battery Compartment

- 1 kW HVAC with 500 W Heater, DC*
- 4 Battery Shelves, 6-String Capacity of 24 HT200 Ah VRLA Batteries
- Master Circuit Breaker String Panel with 6 each 250-amp String Circuit Breaker Switches
 - Battery Cabling and the 250A Circuit Breakers Included
- CommScope Battery Bus Bar Assembly
 - Connection Point for Battery Cabling to the Power Cabinet
- Maximum Cable Size of 4.0 AWG from Battery to Power Cabinet
- Cabinet Light
- Hinged Rear Access Door with Upper and Lower Vents
- Knockouts on Left and Right Sides, Rear
- Top and Side Solar Shields
 - Side Shield Fits Left and Right Sides, Pending Cabinet Site Orientation (one cabinet side shield only)
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
 - Cabinet can use both Electronic and Standard Keyed Puck Locks


Telcordia GR-487 Compliant Safety Agency Listed


* Hardened equipment to -40° C to +65° C



CMC74-36B NiCd Battery Cabinet, 6-Strings, with 1 kW Heater

Model 760250963





CMC Cabinet Order Information

Orderable Number	Description
	CMC74-36B, NiCd Battery Cabinet, 6-String, with 1 kW Heater

Field Replacement Units and Aftermarket Kits

Orderable Number	Description		
Field Replacement Units (FRUs)			
760250922	Handle, Front Door		
760250927	Solar Shield, Top		
760250928	Circuit Breaker, Battery String, 250 A		
760250961	Solar Shield, Side		
760250984	Front Door Assembly, with 1 kW Heater, CMC74-36B		
760253196	NiCd Battery Comp Heater, 1 KW, 48V, CMC		
760253587	Rear Door Assembly, CMC74-36B		
After Market Kits (AMKs)			
760246443	AMK, Interconnect, 3PR, 4/0, 2", CMC74-36B		
760250933	6" High Plinth, Cabinet Mounting		
** Additional AMKs can be found on pages 21-22.			

Cabinet Features

Dimensions:

- Overall 74" H X 37" D X 36" W (standard height)
- With Optional 6" Plinth 80" H X 37" D X 36" W
- Footprint 37" D X 36" W (depth without heater)

Weight: 1019 lbs. (462.3 kg) - for 6-String Cabinet

Weight, as Shipped: 1196 lbs. (542.3 kg)

Note: Cabinet Weights are without Plinth (112.4 lbs. [51 kg]).

Battery Compartment

- 1 kW DC Heater*
 - Note: Cabinet Depth with Heater is 43.7"
- 4 Battery Shelves with Total Capacity for 6 Strings of SAFT TLX+180-8 Ni-Cd batteries, 48V, (172 Ah)
- Master Circuit Breaker String Panel with 6 each 250-amp String Circuit Breaker Switches
 - Battery Cabling and the 250A Circuit Breakers Included
- CommScope Battery Bus Bar Assembly
 - Connection Point for Battery Cabling to the Power Cabinet
 - Maximum Cable Size of 4.0 AWG from Battery to Power Cabinet
- Cabinet Light
- Hinged Rear Access Door with Upper and Lower Vents
- Knockouts on Left and Right Sides, Rear
- Top and Side Solar Shields
 - Side Shield Fits Left and Right Sides, Pending Cabinet Site Orientation (one cabinet side shield only)
- Integrated Puck Lock System Intrusion Prevention, Front and Rear Doors
- Cabinet can use both Electronic and Standard Keyed Puck Locks

Telcordia GR-487 Compliant Safety Agency Listed

* Hardened equipment to -40° C to +65° C



CommScope Cabinet Datasheet CommScope CMC Cabinet Aftermarket Kit (AMK) Options

CommScope CMC Cabinet Aftermarket Kit (AMK) Options



CMC Cabinets Aftermarket (AMK) Options

Category	CommScope Part #.	Description
Cable Management	760241596-KIT	AMK, Bar, Cable Management, Lacer 19" Offset 4"
Cable Glands	760248114	AMK, Single Connection Gland Kit
	760248115	AMK, Raycap Cable Gland, M75,44mm Insert
	760248116	AMK, Raycap Cable Gland, M75 3-Hole
	760248117	AMK, Raycap Cable Gland, M75 (for 12x24 Hybrid)
	760248118	AMK, CEKIT-M63-37-44MM, Cable Entry, BK (for 6x12 hybrid)
	760248119	AMK, CEKIT-1NPT-13-20MM, Cable Entry, BK (for 1/2" coax cable)
Cable Seal	FA-102993-HC3-KIT	AMK, ROXTEC, Cable Seal, CRL 4/4 (for 1/2" coax cable)
Cubic Sedi	FA-102997-HC3-KIT	AMK, ROXTEC, Cable Seal, CRL 4/1 (for either 6x12 or 12x24 hybrid)
Cabinet Mounting /	760250933	AMK, 6" High Plinth, CMC Cabinet Mounting 36" Wide Cabinet
Connection	760246443	AMK, Interconnect, 3PR, 4/0, 2",CMC74-36B
COAY		T:
COAX	F1A-NMNM-3M-P-KIT	Timing Jumper, FSJ1 N-Male to N-Male Coax Jumper (F1A-NMNM-3M-P), 3M
	760253199	AMK, Kit, Arrestor, Coax, Type-N, F, GND BRKT
	7/0020000	AAAK 101111 + T 40VDC 4/0150012
Equipment / Battery Heaters	760238990 760253196	AMK, 1RU Heater Tray, 48VDC 460159213 AMK, NiCd Battery Comp Heater, 1 KW, 48V, CMC
	700233190	AVIK, NICa Ballery Comp Healer, 1 KVV, 46V, CIVIC
	460159115-KIT	AMK, FOC, FIS, Duplex, 1.6mm, Singlemode, UPC, LC-LC, 2M
Fiber Cable	460159116-KIT	AMK, FOC, FIS, Duplex, 1.6mm, Singlemode, UPC, LC-SC, 2M
Tibel Cubie	460160717-KIT	AMK, FOC, FIS, Simplex, 1.6mm, Singlemode, UPC, LC-SC, 2M
	400100717-1011	Tivit, 1 CC, 113, Simplex, 1.5min, Singlemode, of C, EC-EC, Zivi
Fiber Termination Panel/ Fiber Slack Mgt	760253200	AMK, Raycap 2RU FTP Panel, RTF-4575
Fiber Pass through Module	RM-4520-MOD-12-KIT	AMK, 24-Fiber Pass-Through Module
Fuse Holder	460128804	FIU, GMT Fuse Holder, 6P, Bullet
Fuse Panel	760237692-KIT	AMK, Fuse Panel, Westell NPGMT1107, 1RU, 50A
	760246447-KIT	AMK, Fuse Panel, Westell, 200A, NPGMT1107, 100A
	760238570-KIT	AMK, Fuse Panel, Westell NPGMT1305, 20 POS
Laptop Tray	760238305	AMK, Drawer, Laptop, 1RU, Black

Continued on the following page.



CommScope CMC Cabinet Aftermarket Kit (AMK) Options

CMC Cabinets Aftermarket (AMK) Options - Continued

Category	CommScope Part #.	Description
Port Panel, Rear	760253198	AMK, Interchangeable Roxtec Panel, 4-inch, Rear
Power Splitter	S-4-UW-H-NI6-KIT	AMK, 4-Way High Power Splitter 555-6000, N
	42396A-17-KIT	Mounting Bracket for Passive High Power 4-Way Splitter
	760239584-KIT	AMK, Dial Kit, Propane- Asentria 5000-067 - (Site Dependent)
Sensor	760239585-KIT	AMK, Dial Kit, Diesel- Asentria 5000-068 - (Site Dependent
	760239586-KIT	AMK, Pressure Switch, NGAS - Asentria 5006-049 - (Site Dependent)
Sun Shield, Pull Out	760253197	AMK, Sun Shield, Pull Out for CMC
Theft Deterrent	SK-BSP-STDV-AMK	AMK, SES Puck Lock
Top Mount Fiber Storage	760251443	CMC74/85, Top Hat, Fiber Storage

