

# 760255696 | RMM-12AUF-12AUF-SM-ULL



1RU rack mounted Singlemode mesh module with all front facing MPO12 ports. 24, 12f inputs from separate network enclaves to 24, 12f outputs to the desktop with Ultra-Low Loss (ULL) performance

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	FD

## General Specifications

<b>Color</b>	Black
<b>Interface, front</b>	MPO
<b>Interface Feature, front</b>	Shuttered   Unpinned
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Fibers, quantity</b>	288
<b>Total Ports, quantity</b>	48

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

# 760255696 | RMM-12AUF-12AUF-SM-ULL

---

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant/Exempted

