


# 760255049 | PPL-SP-16LC-OM4-PT-BEU



Propel Multimode Splice Cassette, 16LC with internal shutters, OM4 single fiber pigtails, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 4 of the 12 lanes on the Propel Panel blade

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color, front</b>	Aqua
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	16

## Dimensions

<b>Height</b>	67.31 mm   2.65 in
<b>Width</b>	131.013 mm   5.158 in

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.15 dB

## Environmental Specifications

# 760255049 | PPL-SP-16LC-OM4-PT-BEU

---

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** UL

## Packaging and Weights

**Included** Single Fusion Splice Protection Sleeves

**Packaging quantity** 1

## Included Products

103897-000 – SMOUV Fiber Optic Splice Heat Shrink Protective Sleeve for FIST Trays, pack of 100  
SMOUV-1120-02 pcs