

# 760255085 | PPL-SP-24LC-OM4-RPT-AS



Propel Multimode Splice Cassette, 24LC with internal shutters, OM4 ribbon fiber pigtail, pairs straight ULL

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade

Recommended for use with 24f subunit cable

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber cassette with ribbon pigtail
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color, front</b>	Aqua
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Ribbon pigtail
<b>Polarity</b>	Pairs, straight
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Height</b>	67.31 mm   2.65 in
<b>Width</b>	196.012 mm   7.717 in

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.15 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
--------------------------------	---------------------------

# 760255085 | PPL-SP-24LC-OM4-RPT-AS

---

**Safety Standard** UL

## Packaging and Weights

**Included** Mass Fusion Splice Protection Sleeves

**Packaging quantity** 1