

760255087 | PPL-SP-12LC-OM4-PT-BEU-ANT

Propel Multimode Splice Cassette, 12LC with internal shutters, OM4 single fiber pigtails, Method B Enhanced ULL, ANT Splice Protector

- Can be installed and removed from front or rear of panel
- This component requires 3 of the 12 lanes on the Propel Panel blade

Product Classification

Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Aqua
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	12

Dimensions

Height	67.31 mm 2.65 in
Width	97.993 mm 3.858 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.15 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL

Packaging and Weights

Included Single Fusion Splice Protection Sleeves

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

