

# UKVMXMXCD

## Base Product



Ultra Low Loss (ULL) OM5 MPO12 UPC (pinned) to MPO12 UPC (pinned) Fiber Trunk Cable Assembly, 12-Fiber, Armored Indoor Dual Rated (OFNR /LSZH)

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin America | Middle East/Africa | North America

### Portfolio

CommScope®

### Product Type

Fiber trunk cable assembly

### Product Brand

Propel | SYSTIMAX ULL

### Ordering Note

For additional jacket colors, please contact a CommScope Sales Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

## General Specifications

### Connector A, quantity

1

### Color, boot A

Black

### Color, connector A

Lime green

### Connector B, quantity

1

### Color, boot B

Black

### Color, connector B

Lime green

### Construction Type

Armored | Stranded

### Furcation Color

Lime green

### Interface, Connector A

MPO-12/UPC Male

### Interface, Connector B

MPO-12/UPC Male

### Jacket Color

Lime green

### Polarity

Method B Enhanced (ULL)

### Fibers per Subunit, quantity

12

### Total Fibers, quantity

12

## Dimensions

### Breakout Length

22 in

# UKVMXMXCD

|   |          |
|---|----------|
| <b>Cable Assembly Length Range (m)</b>  | 3 – 305  |
| <b>Cable Assembly Length Range (ft)</b> | 10 – 999 |

## Ordering Tree



## Mechanical Specifications

|  |                               |
|--|-------------------------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0°   4.40 lb @ 90° |
|--|-------------------------------|

## Optical Specifications

|                   |                 |
|-------------------|-----------------|
| <b>Fiber Mode</b> | Multimode       |
| <b>Fiber Type</b> | OM5, LazrSPEED® |

## Environmental Specifications

|   |                                      |
|---|--------------------------------------|
| <b>Operating Temperature</b>                        | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Dca                                  |
| <b>Environmental Space</b>                          | Dual Rated LSZH/Riser   Indoor       |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ANATEL        | Compliant  |
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |

# UKVMXMXCD

---

UK-ROHS

Compliant/Exempted



## Included Products

- 760249679  
N-012-MZ-5G-F12AQ/20T/B2 - Fiber indoor cable, LazrSPEED® Riser/LSZH rated, MPO Trunk, interlocking aluminum armored, Multimode OM5, 12 fiber, Feet jacket marking, Lime-green jacket color, B2ca flame rating
- 860659008 - MPO12, ULL, MALE, OM5, LIME, 2MM