

NOVUXTM Specialty Range Closure 100, splice only, no adapters, no splitters, 12 splices, SMOUV® 45mm splice protectors, black, (HMFOC) cable assembly, HMFOC jack to stub, 12-fiber 20FT. Gel-filled, TelSplice connector

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

Product Classification

Regional Availability

Asia | EMEA | Latin America | North America

Regional Availability Note Contact your local CommScope representative for specific availability

Product Type Single-ended, rectangular fiber closure

Product Brand NOVUX™
Product Series SRC100

General Specifications

Cable Capacity, Drop 4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) | 4 Round 1.2–8.0 mm (0.05–0.31 in)

Cable Ports Quantity, total 4 multi-out ports (8 cables)

Cable Sealing Type Compressed gel

Cable Termination Attachments, quantity 2

Closure Sealing Type Hinged with latch
Closure Style Single-ended

Color Black

Mounting Handhole | Partially buried | Pedestal | Wall/Pole Mount, mounting kit

included

Network Area Type Drop

Port Type No adapter | No adapter

Port, quantity 0
Splice Tray Included, quantity 1



Splice Tray Type Included 12-way, heat shrink

Splicing Capacity, maximum 12

Splicing Capacity, Single Fusion, maximum 12

Splicing Type, Supported Single fusion

Splitter Type No splitter

Splitter, quantity 0

Dimensions


 Height
 267 mm | 10.512 in

 Width
 117 mm | 4.606 in

 Depth
 49 mm | 1.929 in

 Cable Entry Drop Port Diameter
 8 mm (0.31 in) mm

Ordering Tree



Material Specifications

Material Type Impact-resistant polymer

Optical Specifications

Fiber Type G.652.D | G.657.A1 | G.657.A2 | G.657.B3

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Above ground | Below ground | Direct burial

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

UV Resistance UV stabilized

Page 3 of 7

Water Resistance Flash test valve at 2 psi (20 kPa)

Packaging and Weights

Packaging quantity 10

Packaging Type Box | Carton

Included Products

88823Y-000 – Gator Fiber Splice Tray Tone Wire Connector

FDSC-GATOR-TEL-SPLICE

NVX-CR-MC-FT-NN – NOVUX™ Cable Termination Unit (CTU) for flat cables with 3x5 to 4x8 mm diameter, metal

clip

NVX-CR-MC-RD-NN – NOVUX™ Cable Termination Unit (CTU) for round cables with 4 to 6,2 mm diameter, metal

clip

88823Y-000 | FDSC-GATOR-TEL-SPLICE

Gator Fiber Splice Tray Tone Wire Connector

Product Classification

Regional Availability Latin America | North America

Product Type Connector kit
Product Series FDSC GATOR

General Specifications

Application For use with FDSC-GATOR Fiber closures

Packaging and Weights

Packaging quantity 100

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



NVX-CR-MC-FT-NN



NOVUX™ Cable Termination Unit (CTU) for flat cables with 3x5 to 4x8 mm diameter, metal clip

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

Product Type Cable termination kit

Product Brand NOVUX™

Product Series CSC

General Specifications

Application For use with CSC Fiber closures

Color Black

Packaging and Weights

Packaging quantity 20

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





NVX-CR-MC-RD-NN



NOVUX™ Cable Termination Unit (CTU) for round cables with 4 to 6,2 mm diameter, metal clip

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

Product Type Cable termination kit

Product Brand NOVUX™

Product Series CSC

General Specifications

Application For use with CSC Fiber closures

Color Black

Packaging and Weights

Packaging quantity 20

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency Classification

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

