

RF-NL7-3-72



Non-Penetrating Roof Frame, 7 ft face, three 3-1/2 in OD x 72 in pipes

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating
Note Four 96 in x 18 in panel antennas per sector
Pipe, quantity 3

Dimensions

Height 1,828.8 mm | 72 in
Face Width 2.134 m | 7 ft
Width 2,133.6 mm | 84 in
Length 2.53 m | 8.3 ft
Pipe Length 1,828.8 mm | 72 in
Pipe Outer Diameter 88.9 mm | 3.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Rubber mats, with or without pipe mounts

RF-NL7-3-72

Packaging quantity 1
Weight, net 271 kg | 597.452 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code