RK-36-3S

Monopole Load Distribution Reinforcement Kit, 3 Sector, 10" to 30" OD, 36" Kicker

Product Classification

Product Type	Reinforcement kit

General Specifications

Mounting	Monopole, 254–762 mm (10–30 in) OD
Sectors, quantity	3

Dimensions

Height	254 mm | 10 in
Length	914.4 mm | 36 in
Mounting Diameter, maximum	762 mm | 30 in
Mounting Diameter, minimum	254 mm | 10 in

Material Specifications

Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included	Attachment hardware | Ring mount
Packaging quantity	1
Weight, net	111.13 kg | 245 lb

Regulatory Compliance/Certifications

Agency	**Classification**

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 23, 2023

CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 23, 2023