

CSC7-E8F6A1BA000



NOVUX™ CSC200 Compact Fiber Closure, splice only, 3 single fiber trays open routing, 4 feeder ports, Xdrop SC/APC adapters, no splitters, with mounting bracket, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	CSC 200

General Specifications

Cable Ports Quantity, total	4 round ports + 12 multi-out ports (24 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Pole Wall
Port Type	SC/APC (Xdrop)
Port, quantity	12
Splice Tray Included, quantity	3
Splice Tray Type Included	48-way, single fiber tray with open routing
Splicing Capacity, maximum	144
Splitter Type	No splitter

CSC7-E8F6A1BA000

Splitter, quantity 0

Dimensions

Height 388.2 mm | 15.283 in

Width 222 mm | 8.74 in

Depth 116 mm | 4.567 in

Environmental Specifications

Environmental Space Outdoor

UV Resistance UV stabilized

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Packaging Type Box | Carton