

FD3-AG432J00GCBP4P



FDH 3000 Fiber Distribution Medium Cabinet, 432F, SC/APC, no splitters, single armor loose tube, 100 ft, 48FF

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	3
Distribution Ports, quantity	432
Fibers per Distribution Cable, quantity	216
Fibers per Feeder Cable, quantity	48
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole
Splitter Slots, quantity	24

Dimensions

Height	1,066.8 mm 42 in
Width	685.8 mm 27 in
Depth	457.2 mm 18 in
Cable Length	30.48 m 100 ft
Enclosure Size	Medium

Material Specifications

Finish	Powder coated
Material Type	Aluminum

FD3-AG432J00GCBP4P

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

