

FD3-PA072J00U3410



FDH 3000 Fiber Distribution Hub in a Pedestal, 72F, SC/APC, no splitters, stranded pigtails, 3 splice trays, 72 splice cap., 6F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

| | |
|------------------------------|-------------------|
| Regional Availability | North America |
| Product Type | Hub in a pedestal |
| Product Series | FDH 3000 |

General Specifications

| | |
|--|---------------------|
| Access | Front Rear |
| Cable Type | Pigtails - Stranded |
| Color | Green |
| Distribution Ports, quantity | 96 |
| Fibers per Feeder Cable, quantity | 6 |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Mounting | Pedestal |
| Splice Tray Included, quantity | 3 |
| Splice Tray Type Included | 24-way, heat shrink |
| Splicing Capacity, maximum | 72 |
| Splitter Slots, quantity | 6 |

Dimensions

| | |
|-----------------------|--------------------|
| Height | 889 mm 35 in |
| Width | 292.1 mm 11.5 in |
| Depth | 368.3 mm 14.5 in |
| Enclosure Size | Small |

FD3-PA072J00U3410

Material Specifications

Material Type Molded plastic

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Included Cable clamps (4)

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

