## FD3-AJ1152J00GGBP6



FDH 3000 Fiber Distribution Large Cabinet, 1152F, SC/APC, no splitters, single armor loose tube, 100 ft, 60FFF

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

Product Series FDH 3000

General Specifications

**Access** Front and rear door

 Cable Type
 Armored - Single Loose Tube

**Color** Putty white

Distribution Cables, quantity 4

**Distribution Ports, quantity** 1152

Fibers per Distribution Cable, quantity 288

Fibers per Feeder Cable, quantity 60

Interface, Input SC

Interface Feature, Input APC

**Mounting** Pad

Splitter Slots, quantity 48

#### Dimensions

**Height** 1,238.25 mm | 48.75 in

**Width** 1,220.47 mm | 48.05 in

**Depth** 497.33 mm | 19.58 in

**Cable Length** 30.48 m | 100 ft

Enclosure Size Large

Material Specifications

**Finish** Powder coated

Material Type Aluminum

COMMSC PE°

# FD3-AJ1152J00GGBP6

### **Environmental Specifications**

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

