

F-CLAMP-D-1B



KwikClamp™ Hanger for power & fiber cables, 34-46 mm, single stack; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3-25 mm flat plate Round Member 8-25 mm

Dimensions

Maximum Stack Height	1
Height	163 mm 6.417 in
Width	57 mm 2.244 in
Length	45 mm 1.772 in
Compatible Cable Diameter Range	34-46 mm
Compatible Diameter, maximum	46 mm 1.811 in
Compatible Diameter, minimum	34 mm 1.339 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

F-CLAMP-D-1B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 30

Weight, gross 5.25 kg | 11.574 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power