


WB-K110-B18



Safety Grated Waveguide Bridge Kit, 12 in x 10 ft, with two 18 ft direct burial posts

Product Classification

Portfolio	CommScope®
Product Type	Waveguide bridge kit
Ordering Note	CommScope® standard product with terms

General Specifications

Application	Direct burial
Cable Runs, quantity	12
Pipe, quantity	2

Dimensions

Height	5,486.4 mm 216 in
Width	304.8 mm 12 in
Length	3048 mm 120 in
Pipe Length	5,486.4 mm 216 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Packaging and Weights

Included	Caps Channel Hardware Posts Support brackets Trapeze
Packaging quantity	1
Weight, net	155 kg 341.716 lb

Regulatory Compliance/Certifications

WB-K110-B18

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

- MF-130 – Direct Burial Pipe Column, 13 ft 4 in
- WB-CY110 – Safety Grated Waveguide Bridge Channel, 12 in x 10 ft
- WB-LB12-3 – Waveguide Bridge Support Bracket, 12 in wide for 3-1/2 in OD legs
- WB-T12-3 – Trapeze Kit, triple tee, 12 in wide, three rungs