

# CSC5-B5A1A1CA000

---



## NOVUX™ CSC150 Compact Fiber Closure, ANT splice protection trays with Island, no adapters, no mounting bracket, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	NOVUX™
<b>Product Series</b>	CSC 150

## General Specifications

<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Pole   Wall
<b>Port Type</b>	No adapter
<b>Splicing Capacity, maximum</b>	72
<b>Splicing Capacity, Single Fusion, maximum</b>	72
<b>Splicing Type, Supported</b>	Single fusion
<b>Splitter Type</b>	No splitter
<b>Splitter, quantity</b>	0

## Dimensions

# CSC5-B5A1A1CA000

---

<b>Height</b>	357 mm   14.055 in
<b>Width</b>	185.4 mm   7.299 in
<b>Depth</b>	115 mm   4.528 in

## Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton