

SSH-3642



PIM-Guard®, SnapTak® Adjustable Hanger, Gen 2. Fits 36.0 mm to 42.0 mm Cables – PIM Free Polymer Construction. No Grommets Required.

Product Classification

Product Type	Hanger kit
Product Brand	PIM-Guard® SnapTak®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Accessories	Hangers
Cables per Hanger	1
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	2
Maximum Stack Height, Coaxial	2
Height	81.32 mm 3.202 in
Width	42 mm 1.654 in
Length	114.21 mm 4.496 in
Compatible Cable Diameter Range	36–42 mm
Compatible Diameter, maximum	42 mm 1.654 in
Compatible Diameter, minimum	36 mm 1.417 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

SSH-3642

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 4.5 cm | 1.772 in

Width, packed 20 cm | 7.874 in

Length, packed 38 cm | 14.961 in

Packaging quantity 10

Weight, gross 0.36 kg | 0.794 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power