

CSC5-B5A1A1CC000



NOVUX™ CSC150 Compact Fiber Closure, trays with island, splice only, no adapters, no splitters, mounting bracket, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	CSC 150

General Specifications

Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Pole Wall
Port Type	No adapter
Splicing Capacity, maximum	72
Splicing Capacity, Single Fusion, maximum	72
Splitter Type	No splitter
Splitter, quantity	0

Dimensions

Height	357 mm 14.055 in
---------------	--------------------

CSC5-B5A1A1CC000

Width	185.4 mm 7.299 in
Depth	115 mm 4.528 in

Environmental Specifications

Environmental Space	Outdoor
UV Resistance	UV stabilized

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1
Packaging Type	Box Carton