



Outdoor Fiber Cable, 6-fiber, multimode, loose tube, blue

## Product Classification

|                              |                       |
|------------------------------|-----------------------|
| <b>Regional Availability</b> | Australia/New Zealand |
| <b>Portfolio</b>             | CommScope®            |
| <b>Product Type</b>          | Fiber OSP cable       |
| <b>Product Series</b>        | O-LN                  |

## General Specifications

|                                     |            |
|-------------------------------------|------------|
| <b>Cable Type</b>                   | Loose tube |
| <b>Subunit Type</b>                 | Gel-filled |
| <b>Jacket Color</b>                 | Blue       |
| <b>Jacket Marking</b>               | Meters     |
| <b>Fibers per Subunit, quantity</b> | 6          |
| <b>Total Fiber Count</b>            | 6          |

## Dimensions

|                             |                  |
|-----------------------------|------------------|
| <b>Diameter Over Jacket</b> | 8.9 mm   0.35 in |
|-----------------------------|------------------|

## Mechanical Specifications

|             |           |
|-------------|-----------|
| <b>Flex</b> | 25 cycles |
|-------------|-----------|

## Optical Specifications

|                   |     |
|-------------------|-----|
| <b>Fiber Type</b> | OM3 |
|-------------------|-----|

## Optical Specifications, Wavelength Specific

|                             |                   |
|-----------------------------|-------------------|
| <b>Standards Compliance</b> | TIA-492AAAC (OM3) |
|-----------------------------|-------------------|

## Environmental Specifications

|                            |                               |
|----------------------------|-------------------------------|
| <b>Environmental Space</b> | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

### Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

