



ReadyPATCH® ULL Multimode OM5 MPO-12 Distribution Module, 6 duplex LC non-keyed red adapters to 1X12f MPO/UPC non-pinned, Method B Enhanced

Product Classification

| | |
|------------------------------|---------------|
| Regional Availability | North America |
| Portfolio | CommScope® |
| Product Type | Fiber module |
| Product Brand | ReadyPATCH® |

General Specifications

| | |
|-------------------------------------|-------------------------|
| Functionality | Breakout |
| Adapters, quantity, front | 6 |
| Adapters, quantity, rear | 1 |
| Color, front | Red |
| Color, rear | Gray |
| Data Module Type | Standard |
| Interface, front | LC/UPC |
| Interface, rear | MPO |
| Interface Feature, rear | MPO Non-Pinned |
| Polarity | Method B Enhanced (ULL) |
| Shuttered | No |
| Total Fibers, quantity | 12 |
| Total Ports, quantity, front | 6 |

Dimensions

| | |
|---------------|--------------------|
| Height | 27.94 mm 1.1 in |
| Width | 129.54 mm 5.1 in |
| Depth | 127 mm 5 in |

Optical Specifications

| | |
|--------------------------------|--------------------------|
| Fiber Mode | Multimode |
| Fiber Type | OM5, LazrSPEED® wideband |
| Insertion Loss, maximum | 0.35 dB |

Environmental Specifications

| | |
|------------------------|---------|
| Safety Standard | c-UL-us |
|------------------------|---------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|