

# FD3-AB096J00JKBP3-US



Enhanced Mini FDH, 96F loaded pole/wall mounted cabinet, SC/APC, PNP splitter capable, OSP Dry Dielectric Loose Tube Cable, 100ft stubs, using a 1x96F distribution cable assembly and a 1x36F feeder, Build America Buy America (BABA) Compliant

- \*CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
Government Funding	Build America Buy America (BABA) coming soon*

## General Specifications

Access	Front
Cable Type	Dry Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	96
Fibers per Distribution Cable, quantity	96
Fibers per Feeder Cable, quantity	36
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole   Wall
Splitter Slots, quantity	8

## Dimensions

Height	584.2 mm   23 in
Width	330.2 mm   13 in
Depth	203.2 mm   8 in

# FD3-AB096J00JKBP3-US

---

Cable Length	30.48 m   100 ft
Enclosure Size	Mini

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

## Environmental Specifications

Environmental Space	Above ground   Aerial
Qualification Standards	Telcordia GR-3123-CORE   Telcordia GR-3125-CORE

## Packaging and Weights

Packaging quantity	1
Packaging Type	Pallet