

FD3-AG432J00PFBP9X-US



Standard FDH3000, 432F loaded pad/vault mounted cabinet, SC/APC, PNP splitter capable, OSP Dry Armored Flat Ribbon Cable, 100 ft stubs, using a 1x432F distribution cable assembly and a 1x144F feeder, Build America Buy America (BABA) Compliant

- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
Government Funding	Build America Buy America (BABA) coming soon*

General Specifications

Access	Front
Cable Type	Armored - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	432
Fibers per Distribution Cable, quantity	432
Fibers per Feeder Cable, quantity	144
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	30

Dimensions

Enclosure Size	Medium
-----------------------	--------

Material Specifications

Finish	Powder coated
---------------	---------------

FD3-AG432J00PFBP9X-US

Material Type Aluminum

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

